

MasterPoint Ultimate and Ultimate Cut



Constructed with a unique disposable container that automatically collects all toxic dust particles. The container is replaceable.

Cold, wet, high speed diamond wheel grinding ensures the electrode always has a polished and even surface. The precise angle produced is important to the quality of welding seams and also reduces the number of re-ignitions between grinding, thus prolonging electrode life.

It is very easy to use; just place the electrode in the holder, set the grinding angle and insert the holder into the combined stick-out/locking device. After grinding and if required the tip can be flattened by placing the electrode in the 90 degree position.

The MasterPoint Wet is available in 220 and 110 volt versions and comes with 250 ml of grinding liquid, diamond wheel, electrode clamps (1.6mm - 3.2mm), electrode holder, disposable container and a stainless steel base.

CE Certified.

Specification

Voltage:	AC110V,220V
Frequency:	50-60Hz
Power:	280W
Motor speed:	4500rpm
Min grinding length:	15mm
Tungsten diameter:	0.8 - 4.0mm
Grinding angle range:	7.5 - 90 degrees